



Abb. 36: Schaltung des vollständigen NF-Verstärkers

- Stückliste:**
- P, Potentiometer 1 M Ω , logarithmisch
 - R₁ = 2 M Ω 1/4 W
 - R₂ = 2 k Ω 1/2 W
 - R₃ = 1,5 M Ω 1/4 W
 - R₄ = 300 k Ω 1/2 W
 - R₅ = 500 k Ω 1/4 W
 - R₆ = 170 Ω 1/2 W
 - R₇ = 1 k Ω 1/2 W
 - Lötösenleisten
 - Buchsen
 - C₁ = 5000 pF
 - C₂ = 50 μ F/6 V (Niedervolt)
 - C₃ = 4 μ F/285 V
 - C₄ = 10 000 pF
 - C₅ = 50 μ F/6 V (Niedervolt)
 - C₆ = 5000 pF
 - U = Übertrager EL 84
 - Rö₁ = EF 89, Rö₂ = EL 84
 - 2 Noval-Röhrenfassungen